

HAFFMANS OGM IN-LINE O₂ GEHALTEMETER

GENERAL PRODUCT INFORMATION

In the beer and beverage industries, the content of dissolved oxygen (DO) is extremely important to both product quality and taste. Excess oxygen (O₂) can compromise the flavor stability and lead to significantly reduced product shelf life.

Because of this, breweries and other beverage manufacturers continuously seek to measure and control the O₂ concentrations throughout production.

The In-line O₂ Gehaltemeter, type OGM, combines high accuracy with excellent measurement stability. This new optical O₂ measurement technology provides greatly improved response times compared to traditional O₂ measuring devices and does not require frequent calibration.

The OGM is available in two measuring ranges:

- Low measuring range (LHO) for accurate DO measurement of beverages < 2,000 ppb (e.g. beer and deaerated water)
- Wide measuring range (WLO) for accurate DO measurement of beverages < 45.0 mg/l (e.g. wort, soft drinks and non-deaerated water)

The OGM can be installed anywhere in the production process where the determination of the dissolved oxygen content is critical to the quality of the product. The O₂ sensor is hygienically designed, and is easily mounted. It is available in two executions:

- Varivent® connection
- 25mm connection (that will fit in a classic 25mm connection typically used with traditional O₂ measuring devices)
- Tri-Clamp 2" connection



The user-friendly control unit can be supplied in either field or panel mounted versions and a maximum of two O₂ sensor can be connected to each control unit.

CUSTOMER BENEFITS

- **Accurate process control**
 - measurement data storage
- **Cost saving**
 - reduction of product losses
 - low maintenance
 - efficient operation of production processes

APPLICATIONS

- **In-line, at critical locations in the production line where the determination of the dissolved O₂ content is required and adjustments within the process can be made**

HAFFMANS OGM

IN-LINE O₂ GEHALTEMETER

TECHNICAL DATA

CONTROL UNIT

Power supply

85-264 V / 50-60 Hz (optional 24 VDC)

Dimensions

235 x 205 x 165 mm / 9.25 x 8.07 x 6.50 in (LxWxH)

Mounting

Wall mounting

O₂ SENSOR

Varivent® connection

84 x 175 mm

25 mm connection

84 x 240 mm

Tri-Clamp 2" connection

84 x 240 mm

O₂ SENSOR LHO

Measuring range

O₂ Measurement 0.0 - 2,000 ppb

Temperature -5.0 - 40.0 °C

Accuracy

O₂ Measurement ±1 ppb + 2 % of m.v.*

Temperature ±0.1°C

Measuring units

ppb, µg/l, ppm, mg/l, % a.s.

Process temperature

max. 110 °C

Process pressure

max. 10 bar(g)/145 psi

Measuring interval

30 sec. (adjustable from 2 - 999 sec.)

Memory capacity

Up to 500 measurements

Protection class

IP-67

* at 20 °C

O₂ SENSOR WLO

0.1 - 45.0 mg/l

-5.0 - 40.0 °C

< 5 % of m.v.*

±0.1°C

SCOPE OF SUPPLY

- Control unit
- O₂ sensor
- Sensor communication cable
- Control unit wall mounting set
- Mains cable
- I/O cable for analog output
- Calibration beaker with spare O-ring
- Instruction manual

OPTIONS

- **NEW: HAFFMANS CONNECT+ INTERFACE MODULE**
Connects Haffmans QC instruments to all modern PLCs with following standards:
PROFIBUS DP, PROFINET, EtherNet/IP, IoT ready!
- Control unit pipe/sensor mounting set (DN 40 - DN 125)
- Control unit panel mounting set
- Certificate of measurement
- Software set (CD + RS cable)
- Welding socket for 25 mm O₂ sensor
- In-line housing with Varivent® connection, inspection glasses and clamps for O₂ sensor with Varivent® connection (pipe dimensions to be specified at time of enquiry)
- O₂ calibration set



Varivent® sensor



25 mm sensor



Tri-Clamp 2"



HAFFMANS B.V.

P.O. BOX 3150, 5902 RD VENLO, NETHERLANDS WWW.FOODANDBEVERAGE.PENTAIR.COM

All Pentair trademarks and logos are owned by Pentair. All other brand or product names are trademarks or registered marks of their respective owners. Because we are continuously improving our products and services, Pentair reserves the right to change specifications without prior notice.

Pentair is an equal opportunity employer.

haffmans-ogm-2052-en ©2020 Pentair, All Rights Reserved.

